


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
E	ECN 9971; REMOVE PIN MARKING FROM CONNECTOR FACE P1&J1. REMOVE ROHS COMPLIANT STATEMENT.	07/15/2019	B.GATES



MODEL NUMBER	LENGTH	
	FEET	METERS
DK226MF-3	3.0	0.91
DK226MF-6	6.0	1.83
DK226MF-10	10.0	3.05
DK226MF-15	15.0	4.57
DK226MF-20	20.0	6.10
DK226MF-25	25.0	7.62

WIRING MAP		
"J1"	COLOR	"P1"
1	BLACK	1
2	BROWN	2
3	WHITE	3
4	ORANGE	4
5	YELLOW	5
6	LT. GREEN	6
SHELL	DRAIN	SHELL

- NOTES:
- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 - CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 > 12 [305] ≤ 60 [1524] = +2 [51] / -0 > 60 [1524] ≤ 120 [3048] = +4 [102] / -0 > 120 [3048] ≤ 300 [7620] = +6 [152] / -0 > 300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2[5.08] .XX = ± .02[.51] .XXX = ± .005[.13]	APPROVALS	DATE		50 HIGH STREET NORTH ANDOVER, MA 01845
	DRAWN BY TJC	9/2/00		
	CHECKED BY DFP	9/7/00	PRODUCT DESCRIPTION CBL MD6 MALE/ MD6 FEMALE	
	APPROVED BY RC	9/12/00		SIZE A FSCM NO. 43321 DWG. NO. DK226MF REV. E
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SCALE: NONE CAD FILE: DK226MF.SLDDRW	SHEET 1 OF 1