


REVISION

ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	06/03/2024	KGLEBOVA	GUTTADAURO



"P1"



"P2"

SEE NOTE 1
MARKING: AES/EBU DIGITAL AUDIO DMX CABLE
110 OHM AWG24 X 1 PAIR OFC

NOTES:

1. CABLE: 2P*24AWG(7/0.20±0.008mm)TOFC+FILLER+PP+AL/MYLAR+DRAIN (7/0.20TPFC)+ BRAID(16*10/0.12TOFC),
JACKET: HIGH-FLEX PVC, OD: .354±.008 [9.0±0.2].
2. CONTACT MATERIAL P1, P2: COOPER ALLOY, SILVER PLATING.
3. IMPEDENCE: 110 OHMS.
4. INSTALLATION TEMPERATURE RANGE: 0°C TO ~50 °C.
5. OPERATION TEMPERATURE RANGE: -20°C TO ~60 °C.
6. VOLTAGE RATING: 30V.
7. ELECTRICAL TEST: 100% OPEN AND SHORT TEST.
8. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
9. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.

REGULATORY COMPLIANCE:
EU ROHS DIRECTIVE (MOST RECENT RELEASED VERSION).

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

P1	WIRING MAP	P2
1		1 DRAIN
SHELL		SHELL
2		2 WT
3		3 OR
4		4 WT
5		5 BL



TABLE 1

ITEM NO	LENGTH	
	METERS [mm]	FEET [IN]
DMX512MM-BLK-10	0.305 [+35/-15]	1 [+1.38/-0.59]
DMX512MM-BLK-15	4.57 [+35/-30]	15 [+1.38/-1.18]
DMX512MM-BLK-50	15.24 [+80]	50 [+3.15]

UNLESS OTHERWISE SPECIFIED
LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:
X = ±.2 [5]
XX = ±.02 [0.5]
XXX = ±.005 [0.13]

FRACTIONS
± 1/32
ANGLES ± 1°

CABLE LENGTH TOLERANCES:
≤12 [305] = ±1 [25] / -0
>12 [305] ≤ 60 [1524] = ±2 [51] / -0
>60 [1524] ≤ 120 [3048] = ±4 [102] / -0
>120 [3048] ≤ 300 [7620] = ±6 [152] / -0
>300 [7620] = ±5% / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY
AND SUBJECT TO CHANGE WITHOUT NOTICE
UN-DIMENSIONED/NON-CRITICAL FEATURES
MAY VARY IN SIZE AND LOCATION
COLORS MAY VARY

L-com
an INFINITE® brand

Website: www.L-com.com
Phone: 1.800.341.5266 | 1.978.682.6936



INTERPRET ALL DIMENSIONS AND
TOLERANCES PER ASME Y14.5

SCALE
NONE

1 OF 1

SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
A	43321	KGLEBOVA	DMX512MM-BLK	A