


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	4/6/12	D.GRIFFIN



RoHS Compliant ✓

NOTES:
 MATERIAL:
 BODY: NICKEL PLATED BRASS.
 LANYARD: STAINLESS STEEL, NYLON COATED.
 APPLICATION: ST CONNECTOR
 COMPONENT ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN A POLY BAG.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	APPROVALS DRAWN BY D.FRISIELLO	DATE 3/1/12		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	CHECKED BY D.GUITADAURO APPROVED BY D.GALLAGHER	DATE 3/1/12 3/1/12		CATEGORY FIBER OPTICS
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	PRODUCT DESCRIPTION DUST COVER MIL ST W/LANYARD	SIZE A
FSCM NO. 43321		DWG. NO. DSTCP-RSTADPTN	REV. A	SCALE: NONE CAD FILE: DSTCP-RSTADPTN.SLDDRW SHEET 1 OF 1