



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
E	ECN 8257; CHANGE DVI ICON TO THE RIGHT ORIENTATION	2/18/2016	B.ZHANG
F	ECN 9038; CHANGE ENCAPSULATED FERRITE BEAD FROM MTN-228 TO MTN-286	01/03/2018	B.ZHANG



PART NUMBER	LENGTH	
	METERS	FEET
DVIDS-RA2-0.5M	0.5	[1.64]
DVIDS-RA2-1M	1.0	[3.28]
DVIDS-RA2-2M	2.0	[6.56]
DVIDS-RA2-3M	3.0	[9.84]
DVIDS-RA2-4M	4.0	[13.12]
DVIDS-RA2-5M	5.0	[16.41]

- NOTES:**
- CABLE ASSEMBLY TO BE TESTED FOR CONTINUITY
 - CABLE ASSEMBLY TO BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPEC. PS-0031.
 - DUST COVERS INSTALLED FOR SHIPPING (NOT SHOWN).

REGULATORY COMPLIANCE:
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] ≤+1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE		50 HIGH STREET NORTH ANDOVER, MA 01845
	DRAWN BY D. CASTRO	10/19/11		CATEGORY
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [1.51] .XXX = ±.005 [1.3]	CHECKED BY D. PARHAM	10/19/11	PRODUCT DESCRIPTION	CBL DVI-D SL RA
PROJECTION	APPROVED BY P. MCNEIL	10/20/11	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	SIZE A
	COLOR VARIATIONS MAY OCCUR	REF	SIZE A	FSCM NO. 43321
			SCALE: NONE	DWG. NO. DVIDS-RA2-M
			CAD FILE: DVIDS-RA2-M.SLDRW	REV. F
				SHEET 1 OF 1