


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	11/9/11	D.GRIFFIN
B	ECN 5837: ADDED LOGO	11/16/11	D. CASTRO
C	ECN8182: UPT DWG FROM MOLDED THUMBSCREW TO METAL THUMBSCREW	11/30/2015	B.ZHANG
D	ECN 9538: REMOVE THE EXCESS KNURL FOR DVI M RA LFT EXIT END	11/28/2018	B.GATES



"P1"	WIRE MAP	"P2"
19		19 (GND)
18		18 (LT. GREEN)
17		17 (BLACK)
10		10 (YELLOW)
9		9 (BROWN)
11		11 (GND)
15		15 (BLACK)
14		14 (BROWN)
2		2 (RED)
1		1 (ORANGE)
3		3 (GND)
22		22 (GND)
23		23 (LT. BLUE)
24		24 (WHITE)
16		16 (ORANGE)
7		7 (YELLOW)
6		6 (WHITE)
SHELL		SHELL (SHIELD DRAIN WIRE)

NOTES:

1. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
2. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.
3. DUST COVERS INSTALLED FOR SHIPPING (NOT SHOWN).

REGULATORY COMPLIANCE:
CE2011/65/EU (RoHS DIRECTIVE)

MODEL NUMBER	LENGTH	
	FEET	METERS
DVIDS-RA3-1	1.0	0.3
DVIDS-RA3-3	3.0	0.91
DVIDS-RA3-5	5.0	1.52
DVIDS-RA3-10	10.0	3.05
DVIDS-RA3-15	15.0	4.57

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 > 12 [305] ≤ 60 [1524] = +2 [51] / -0 > 60 [1524] ≤ 120 [3048] = +4 [102] / -0 > 120 [3048] ≤ 300 [7620] = +6 [152] / -0 > 300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [1.51] .XXX = ± .005 [1.13]	APPROVALS DRAWN BY D. PARHAM CHECKED BY D. CASTRO APPROVED BY P. McNEIL	DATE 10/26/2011 11/07/2011 11/08/2011	50 HIGH STREET NORTH ANDOVER, MA 01845	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY			CATEGORY AUDIO/VIDEO
	PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321
	PRODUCT DESCRIPTION CA-DVI SL M/M RA LFT EXIT		DWG. NO. DVIDS-RA3	REV. D
SCALE: NONE		CAD FILE: DVIDS-RA3.SLDDRW	SHEET 1 OF 1	