



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	12/21/11	D.GRIFFIN
B	ECN8182; UPT DWG FROM MOLDED THUMBSCREW TO METAL THUMBSCREW	11/30/2015	B.ZHANG
C	ECN_8257; CHANGE DVI ICON TO RIGHT ORIENTATION	2/18/2016	B.ZHANG
D	ECN 9038; CHANGE ENCAPSULATED FERRITE BEAD FROM MTN-228 TO MTN-286	01/03/2018	B.ZHANG



PART NUMBER	LENGTH	
	FEET	METERS
DVIDS-RAZ-1	1.0	[.30]
DVIDS-RAZ-3	3.0	[.91]
DVIDS-RAZ-5	5.0	[1.52]
DVIDS-RAZ-10	10.0	[3.05]
DVIDS-RAZ-15	15.0	[4.57]

- NOTES:**
- CABLE ASSEMBLY TO BE TESTED FOR CONTINUITY
 - CABLE ASSEMBLY TO BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPEC. PS-0031.
 - DUST COVERS INSTALLED FOR SHIPPING (NOT SHOWN).

REGULATORY COMPLIANCE:
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D. PARHAM	12/16/2011		CATEGORY
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [1.51] .XXX = ±.005 [1.3]	CHECKED BY D. FRISIELLO	12/16/2011	PRODUCT DESCRIPTION	CBL DVI-D SL RA LSZH
PROJECTION	APPROVED BY P. McNEIL	12/16/2011	SIZE	A
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		FSCM NO.	43321
	COLOR VARIATIONS MAY OCCUR		DWG. NO.	DVIDS-RAZ
	REF		SCALE: NONE	CAD FILE: DVIDS-RAZ.SLDRW
				SHEET 1 OF 1