

6

5

4



3

2

1

PIN OUT

CONN	WIRE COLOR	WIRE TYPE
1	WHITE	1P+D+AL+MY
2	BROWN	
3	DRAIN	
4	WHITE	1P+D+AL+MY
5	RED	1C
6	RED	
7	PURPLE	1C
8		
9	WHITE	1P+D+AL+MY
10	GREEN	
11	DRAIN	1P+D+AL+MY
12	WHITE	
13	BLUE	1P
14	YELLOW	
15	ORANGE	1C
16	WHITE	1P+D+AL+MY
17	WHITE	
18	BLACK	1P+D+AL+MY
19	DRAIN	
20	WHITE	1P+D+AL+MY
21	ORANGE	
22	DRAIN	1P+D+AL+MY
23	YELLOW	
24	WHITE	



NOTES:

1. WATERPROOF RATING: IP67
2. MATERIAL:
 - a. HOUSING: ABS, BLACK
 - b. PIN: COPPER ALLOY, GOLD PLATED
 - c. GASKET: EPDM, BLACK
 - d. SCREW: STEEL, NICKEL PLATED
 - e. CABLE: UL20276
(1P*28#+D+AL+MYLAR)*7C+1P*28#+3C*28#+AL+B,
COLOR: BLACK, OD: 8.5mm
3. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
4. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.

REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION).

ITEM NUMBER	LENGTH	
	METERS	FEET
DVWPDDL-MM-1M	1.0	3.28
DVWPDDL-MM-3M	3.0	9.84
DVWPDDL-MM-4M	4.0	13.12

UNLESS OTHERWISE SPECIFIED
LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:

X = ±.2 [5]	FRACTIONS
.XX = ±.02 [0.5]	± 1/32
.XXX = ±.005 [0.13]	ANGLES ± 1°

CABLE LENGTH TOLERANCES:
≤12 [305] = +1 [25] / -0
>12 [305] ≤ 60 [1524] = +2 [51] / -0
>60 [1524] ≤ 120 [3048] = +4 [102] / -0
>120 [3048] ≤ 300 [7620] = +6 [152] / -0
>300 [7620] = +5% / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY
AND SUBJECT TO CHANGE WITHOUT NOTICE.
UN-DIMENSIONED/NON-CRITICAL FEATURES
MAY VARY IN SIZE AND LOCATION
COLORS MAY VARY**L-com®**
an INFINIT® brandWebsite: www.L-com.com
Phone: 1.800.341.5266 | 1.978.682.6936INTERPRET ALL DIMENSIONS AND
TOLERANCES PER ASME Y14.5

SCALE NONE SHEET 1 OF 1

DESCRIPTION

WATERPROOF DVI-D CABLE, DUAL LINK, MALE TO MALE

SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
A	43321	HBAKKE	DVWPDDL-MM	B

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE
WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE
EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW
PROHIBITED.

6

5

4

3

2

1