

6

5

4


3

2

1

PIN OUT

CONN	WIRE COLOR	WIRE TYPE
1	WHITE	1P+D+AL+MY
2	BROWN	
3	DRAIN	
4		
5		
6	RED	1C
7	PURPLE	1C
8		
9	WHITE	1P+D+AL+MY
10	GREEN	
11	DRAIN	
12		
13		
14	YELLOW	1P
15	ORANGE	
16	WHITE	1C
17	WHITE	1P+D+AL+MY
18	RED	
19	DRAIN	
20		
21		
22	DRAIN	1P+D+AL+MY
23	BLUE	
24	WHITE	



NOTES:

- WATERPROOF RATING: IP67, UNMATED
- MATERIAL:
 - HOUSING: THERMOPLASTIC, BLACK
 - PIN: COPPER ALLOY, GOLD PLATED
 - GASKET: RUBBER, BLACK
 - SCREW: STEEL, NICKEL PLATED
 - CABLE: UL20276
(1P*28#+D+AL+MYLAR)*4C+(1P+3C)*28#+AL+B,
COLOR: BLACK, OD: 7.3mm
- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.

REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION).

ITEM NUMBER	LENGTH	
	METERS	FEET
DVWPSL-MM-1M	1.0	3.28
DVWPSL-MM-3M	3.0	9.84
DVWPSL-MM-4M	4.0	13.12

UNLESS OTHERWISE SPECIFIED
LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERSTOLERANCES:
X = ±.2 [5] FRACTIONS
.XX = ±.02 [0.5] ± 1/32
.XXX = ±.005 [0.13] ANGLES ± 1°CABLE LENGTH TOLERANCES:
≤12 [305] = +1 [25] / -0
>12 [305] ≤ 60 [1524] = +2 [51] / -0
>60 [1524] ≤ 120 [3048] = +4 [102] / -0
>120 [3048] ≤ 300 [7620] = +6 [152] / -0
>300 [7620] = +5% / -0ALL DIMENSIONS ARE FOR REFERENCE ONLY
AND SUBJECT TO CHANGE WITHOUT NOTICE.
UN-DIMENSIONED/NON-CRITICAL FEATURES
MAY VARY IN SIZE AND LOCATION
COLORS MAY VARY**L-com**
an INFINIT® brandWebsite: www.L-com.com
Phone: 1.800.341.5266 | 1.978.682.6936INTERPRET ALL DIMENSIONS AND
TOLERANCES PER ASME Y14.5

SCALE NONE SHEET 1 OF 1

DESCRIPTION

WATERPROOF DVI-D CABLE, SINGLE LINK, MALE TO MALE

SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
A	43321	HBAKKE	DVWPSL-MM	B

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE
WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE
EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW
PROHIBITED.

6

5

4

3

2

1