


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	2/9/18	D.FRISIELLO



NOTES:

- CABLE RANGE: .271" / .330"
- ASSEMBLED OVERALL LENGTH IS APPROX. 3.3"
- MATERIALS AND FINISH:  
 EXTERNAL PARTS: ALUMINUM/ELECTROLESS NICKEL, (BLACK)  
 INTERNAL PARTS: ALUMINUM  
 MISCELLANEOUS HARDWARE: STAINLESS STEEL  
 SEAL: SILICONE  
 LANYARD: STAINLESS STEEL (NYLON COAT)
- LANYARD LENGTH: APPROXIMATELY 6.0"
- RATING: IP-68, WHEN MATED OR DUST CAP IS ENGAGED.  
 PERFORMANCE MEETS OR EXCEEDS CATEGORY 6 ANSI/EIA 568-C.2
- ALL DIMENSIONS ARE FOR REFERENCE ONLY.
- PARTS SHIPPED UNASSEMBLED.
- SUPPLIED PLUG FINISH, 50μIN GOLD OVER 100μIN NICKEL.
- COMPONENT SHALL BE INDIVIDUALLY PACKAGED  
 IN ACCORDANCE WITH L-COM SPECIFICATION LSP-010-1

**REGULATORY COMPLIANCE:**  
 CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [1.51] .XXX = ±.005 [1.13]	APPROVALS DRAWN BY D.FRISIELLO CHECKED BY D.GUITADAURO APPROVED BY D.GUITADAURO	DATE 2/6/18 2/9/18 2/9/18	50 HIGH STREET NORTH ANDOVER, MA 01845	
	PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR	CATEGORY TELECOM/MODULAR	PRODUCT DESCRIPTION C6 PLUG EN .271-.330 W/DUST CAP
SCALE: NONE		FSCM NO. <b>A</b> 43321	DWG. NO. ECSA4219UB0	REV. <b>A</b>
CAD FILE: ECSA4219UB0.SLDDRW		SHEET 1 OF 1		