


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	7/31/17	D.FRISIELLO



NOTES:

- MATERIAL:**  
EXTERNAL PARTS: ALUMINUM/BLACK ANODIZED  
INTERNAL PARTS: ALUMINUM  
MISC. HARDWARE: STAINLESS STEEL  
SEALS: SILICONE/NITRILE
  - MISCELLANEOUS:**  
RATING: IP-68  
PERFORMANCE MEETS OR EXCESS CATEGORY 6 ANSI/EIA 568-C.2 SPECIFICATIONS.
  - ALL DIMENSIONS ARE FOR REFERENCE ONLY.
  - COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION LSP-010-1
- REGULATORY COMPLIANCE:  
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [51] .XXX = ±.005 [1.27]	APPROVALS D.FRISIELLO	DATE 6/26/17			50 HIGH STREET NORTH ANDOVER, MA 01845	
	CHECKED BY M.MARTINEZ	7/21/17	CATEGORY TELECOM/MODULAR			
	APPROVED BY D.GUITADAURO	7/21/17	PRODUCT DESCRIPTION C6 JAM NUT SEALED ANOD			
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. ECSC0201U00	REV. <b>A</b>
PROJECTION 		SCALE: NONE		CAD FILE: ECSC0201U00.SLDDRW		
SHEET 1 OF 1						