


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| REVISIONS | | | |
|-----------|-----------------|---------|----------|
| REV | DESCRIPTION | DATE | APPROVED |
| A | INITIAL RELEASE | 6/28/17 | R.CLARK |
| | | | |
| | | | |



NOTES:

1. CABLE RANGE: ϕ .190" TO ϕ .270"
ASSEMBLED OVERALL LENGTH IS APPROX. 4.06".
2. MATERIAL:
CONNECTOR: ALUMINUM, ZINC NICKEL (OLIVE DRAB).
HARDWARE: STAINLESS STEEL.
SEALS: SILICONE/NITRILE.
LANYARD: STAINLESS STEEL (NYLON COATED).
3. RATED IP-68.
PERFORMANCE MEETS OR EXCEEDS CATEGORY 6 ANSI/EIA 568-C.
4. ALL DIMENSIONS ARE FOR REFERENCE ONLY.
5. COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION LSP-010-1. SHIPS UNASSEMBLED.

| | | | | |
|---|--|----------------------------|---|--|
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% | APPROVALS | DATE | | 50 HIGH STREET NORTH ANDOVER, MA 01845 |
| | DRAWN BY R.CLARK | 6/28/17 | | CATEGORY TELECOM/MODULAR |
| ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [.51] .XXX = ± .005 [0.13] | CHECKED BY M.MARTINEZ | 7/20/2017 | PRODUCT DESCRIPTION C6 RCP SHLD ZNNI .190-.270 DC | |
| | APPROVED BY DJG | 7/21/2017 | | |
| PROJECTION | CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY | COLOR VARIATIONS MAY OCCUR | SIZE A FSCM NO. 43321 DWG. NO. ECSP5103UA0 | REV. A SCALE: NONE CAD FILE: ECSP5103UA0.SLDDRW SHEET 1 OF 1 |