


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	2/9/18	D.FRISIELLO



**NOTES:**

1. CABLE RANGE:  $\phi$ .271" TO  $\phi$ .330"  
ASSEMBLED OVERALL LENGTH IS APPROX. 4.06".
2. MATERIAL:  
CONNECTOR: ALUMINUM/ELECTROLESS NICKEL, (BLACK).  
HARDWARE: STAINLESS STEEL.  
SEALS: SILICONE/NITRILE.  
LANYARD: STAINLESS STEEL (NYLON COATED).
3. RATED IP-68.  
PERFORMANCE MEETS OR EXCEEDS CATEGORY 6 ANSI/EIA 568-C.
4. ALL DIMENSIONS ARE FOR REFERENCE ONLY.
5. COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION LSP-010-1. SHIPS UNASSEMBLED.

**REGULATORY COMPLIANCE:**  
CE2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE	 50 HIGH STREET NORTH ANDOVER, MA 01845				
	DRAWN BY D.FRISIELLO	2/6/18					
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [51] .XXX = ± .005 [1.27]	CHECKED BY D.GUITADAURO	2/9/18	CATEGORY TELECOM/MODULAR				
	APPROVED BY D.GUITADAURO	2/9/18	PRODUCT DESCRIPTION C6 RCP SHLD EN .271-.330 DCAP				
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	<table border="1"> <tr> <td>SIZE <b>A</b></td> <td>FSCM NO. <b>43321</b></td> <td>DWG. NO. ECSP5209UB0</td> <td>REV. <b>A</b></td> </tr> </table>	SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. ECSP5209UB0	REV. <b>A</b>
SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. ECSP5209UB0	REV. <b>A</b>				
SCALE: NONE		CAD FILE: ECSP5209UB0.SLDDRW	SHEET 1 OF 1				