


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	04/19/2023	HBAKKE	PHOSPODAR




12X LC/UPC CONNECTORS
IL≤0.3dB, RL≥50dB

BREAK OUT LEADS
2.0mm LSZH LOOSE TUBE

12 FIBER CABLE
9/125 SINGLE MODE OS2
LOW SMOKE ZERO HALOGEN
6.2mm OD

12X SC/UPC CONNECTORS
IL≤0.3dB, RL≥50dB

∅ .24in±.01 [6.2mm±0.3]





CABLE TECHNICAL PARAMETERS		
FIBER COUNT		12
FIBER TYPE		SINGLE MODE OS2
CORE DIAMETER (µm)		9
CLADDING DIAMETER (µm)		125
CABLE	OD in[mm]	.24 [6.2]
	MATERIAL	LSZH
BUFFER	OD in[mm]	.03 [.85]
	MATERIAL	LSZH
MAX. TENSILE STRENGTH (N)	SHORT TERM	480
	LONG TERM	240
MIN. BENDING RADIUS	DYNAMIC in[mm]	.79 [20.0]
	STATIC in[mm]	.39 [10.0]
MAX. CRUSH RESISTANCE (N/100mm)	SHORT TERM	1000
	LONG TERM	300
COLOR		BLACK
STRENGTH MEMBERS		ARAMID YARN

ITEM NUMBER	LENGTH	
	METERS	FEET
FCA-12S2LCUSCUD2-3	3.0	9.84
FCA-12S2LCUSCUD2-5	5.0	16.40
FCA-12S2LCUSCUD2-10	10.0	32.81
FCA-12S2LCUSCUD2-15	15.0	49.21
FCA-12S2LCUSCUD2-20	20.0	65.62

NOTES:
1. ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).

REGULATORY COMPLIANCE:
EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [5] ANGLES ± 1° .XXX = ± .005 [1.3]	APPROVALS	DATE	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	DRAWN BY HBAKKE	04/19/2023	
CHECKED BY DMAY	04/19/2023	CATEGORY FIBER OPTICS	
APPROVED BY REVANGELIS	04/19/2023	PRODUCT DESCRIPTION 12 Strand LC/UPC to SC/UPC 9/125 SM OS2, 6.2mm Distribution Cable, 2.0mm Breakout 0.5M, LSZH	
THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	SIZE A	CAGE CODE 43321
COLOR VARIATIONS MAY OCCUR	ITEM NO. FCA-12S2LCUSCUD2	SCALE: NONE	CAD FILE: FCA-12S2LCUSCUD2.SLDRW
			SHEET 1 OF 1