


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	08/11/2021	PHOSPODAR





50/125 MULTIMODE OM4 DUPLEX FIBER CABLE  
LOW SMOKE ZERO HALOGEN  
COLOR: VIOLET

ITEM NO.	LENGTH	
	METER	FEET
FCA-LCLC-DPM4Z-01	1.0	3.28
FCA-LCLC-DPM4Z-02	2.0	6.56
FCA-LCLC-DPM4Z-03	3.0	9.84
FCA-LCLC-DPM4Z-05	5.0	16.40
FCA-LCLC-DPM4Z-07	7.0	22.97
FCA-LCLC-DPM4Z-10	10.0	32.81
FCA-LCLC-DPM4Z-15	15.0	49.21

**NOTES:**

1. LC CONNECTOR POLISH TYPE: UPC.
2. ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

**REGULATORY COMPLIANCE:**  
EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5]   FRACTIONS ± 1/32 .XX = ± .02 [.5]   ANGLES ± 1° .XXX = ± .005 [.13]	APPROVALS DRAWN BY: DZINN CHECKED BY: DFRISIELLO APPROVED BY: PHOSPODAR	DATE 08/11/2021 08/11/2021 08/11/2021	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
	THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR		CATEGORY <b>FIBER OPTICS</b>
		SIZE: <b>A</b> SCALE: NONE	CAGE CODE: <b>43321</b> CAD FILE: FCA-LCLC-DPM4Z.SLDDRW	ITEM NO.: <b>FCA-LCLC-DPM4Z</b> REV.: <b>A</b> SHEET 1 OF 1