


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	08/09/2023	HBAKKE	PHOSPODAR



ITEM NUMBER	LENGTH	
	METERS	FEET
FCA-LCLC-SPLCV-01	1.0	3.28
FCA-LCLC-SPLCV-05	5.0	16.40

**NOTES:**

- CONNECTOR ASSEMBLY POLISH TYPE: PC
- ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.

**REGULATORY COMPLIANCE:**

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION).

<p>UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]</p> <p>OVERALL CABLE LENGTH TOLERANCE:  <math>\leq 12</math> [305] = +1 [25] / -0  <math>&gt; 12</math> [305] <math>\leq 60</math> [1524] = +2 [51] / -0  <math>&gt; 60</math> [1524] <math>\leq 120</math> [3048] = +4 [102] / -0  <math>&gt; 120</math> [3048] <math>\leq 300</math> [7620] = +6 [152] / -0  <math>&gt; 300</math> [7620] = +5% / -0</p> <p>ALL OTHER DIMENSIONAL TOLERANCES:  .X = <math>\pm .2</math> [5]   FRACTIONS <math>\pm 1/32</math>  .XX = <math>\pm .02</math> [.5]   ANGLES <math>\pm 1^\circ</math>  .XXX = <math>\pm .005</math> [.13]</p> <p>THIRD-ANGLE PROJECTION</p>	APPROVALS	DATE	<p>50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936</p>
	DRAWN BY HBAKKE	08/09/2023	
	CHECKED BY DMAY	08/09/2023	
	APPROVED BY TCAHALANE	08/09/2023	
	CATEGORY		FIBER OPTIC
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUCT DESCRIPTION
	COLOR VARIATIONS MAY OCCUR		FIBER OPTIC PATCH CABLE LC/PC-LC/PC SIMPLEX 100/140 LARGE CORE MULTIMODE FIBER 3.0MM PVC
	SIZE A	CAGE CODE 43321	ITEM NO. FCA-LCLC-SPLCV
	SCALE: NONE		CAD FILE: FCA-LCLC-SPLCV.SLDRW
			SHEET 1 OF 1