


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| REVISIONS | | | |
|-----------|-----------------|------------|-----------|
| REV | DESCRIPTION | DATE | APPROVED |
| A | INITIAL RELEASE | 09/28/2021 | PHOSPODAR |
| | | | |
| | | | |



| PART NUMBER | LENGTH METER [FEET] |
|-------------------|---------------------|
| FCA-M1SR-SCST-01M | 1.0 [3.28] |
| FCA-M1SR-SCST-02M | 2.0 [6.56] |
| FCA-M1SR-SCST-03M | 3.0 [9.84] |
| FCA-M1SR-SCST-05M | 5.0 [16.40] |
| FCA-M1SR-SCST-10M | 10.0 [32.81] |
| FCA-M1SR-SCST-15M | 15.0 [49.21] |

NOTES:

- SC CONNECTOR ASSEMBLY POLISH TYPE: UPC.
ST CONNECTOR ASSEMBLY POLISH TYPE: UPC.
- ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.

| | | | |
|---|--|---|---|
| <p>UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]</p> <p>OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0</p> <p>ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13]</p> <p>THIRD-ANGLE PROJECTION</p> | <p>APPROVALS</p> <p>DRAWN BY: MVEERAPPAN</p> <p>CHECKED BY: DFRISIELLO</p> <p>APPROVED BY: PHOSPODAR</p> | <p>DATE</p> <p>09/28/2021</p> <p>09/28/2021</p> <p>09/28/2021</p> | <p>L-com an INFINITO brand</p> <p>50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936</p> |
| | <p>CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY</p> <p>COLOR VARIATIONS MAY OCCUR</p> | <p>CATEGORY</p> <p>FIBER OPTICS</p> <p>PRODUCT DESCRIPTION</p> <p>CA SC-ST 62.5/125 MULTIMODE</p> | <p>SIZE: A</p> <p>CAGE CODE: 43321</p> <p>ITEM NO.: FCA-M1SR-SCST</p> <p>SCALE: NONE CAD FILE: FCA-M1SR-SCST.SLDDRW</p> |