


8 7 6 5 4 3 2 1



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| REVISIONS | | | |
|-----------|-----------------|------------|-----------|
| REV. | DESCRIPTION | DATE | APPROVED |
| A | INITIAL RELEASE | 10/21/2022 | PHOSPODAR |



| ITEM NUMBER | LENGTH METER [FEET] |
|-------------------|------------------------|
| FCA-M1SZ-STST-01M | 1.0 [3.28] |
| FCA-M1SZ-STST-03M | 3.0 [9.84] |
| FCA-M1SZ-STST-05M | 5.0 [16.40] |
| FCA-M1SZ-STST-10M | 10.0 [32.81] |

- NOTES:
1. ST CONNECTOR ASSEMBLY POLISH TYPE: UPC.
 2. ALL CONNECTORS SUPPLIED WITH A DUST CAP INSTALLED, NOT SHOWN.
 3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IAW L-COM SPECIFICATION PS-0031.

| | | | |
|---|--------------------------------|-------------------------------|---|
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13] | APPROVALS DRAWN BY DZINN | DATE 10/21/2022 |  50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936 |
| | CHECKED BY DFRISIELLO | DATE 10/21/2022 | |
| THIRD-ANGLE PROJECTION  | APPROVED BY JJOHNSTON | DATE 10/21/2022 | PRODUCT DESCRIPTION FIBER PATCH CABLE ASSY, 62.5/125 MULTIMODE, OM1, LSZH, STU-STU |
| CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY | | COLOR VARIATIONS MAY OCCUR | SCALE: NONE CAD FILE: FCA-M1SZ-STST.SLDDRW SHEET 1 OF 1 |
| SIZE A | | CAGE CODE 43321 | ITEM NO. FCA-M1SZ-STST |