


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	09/28/2021	PHOSPODAR



PART NUMBER	LENGTH METER [FEET]
FCA-M3SR-STST-01M	1.0 [3.28]
FCA-M3SR-STST-02M	2.0 [6.56]
FCA-M3SR-STST-03M	3.0 [9.84]
FCA-M3SR-STST-05M	5.0 [16.40]
FCA-M3SR-STST-07M	7.0 [22.97]
FCA-M3SR-STST-10M	10.0 [32.81]
FCA-M3SR-STST-15M	15.0 [49.21]

NOTES:

- ST CONNECTOR ASSEMBLY POLISH TYPE: UPC.
- ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.

<p>UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]</p> <p>OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0</p> <p>ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13]</p> <p>THIRD-ANGLE PROJECTION</p>	<p>APPROVALS</p> <p>DRAWN BY MVEERAPPAN</p> <p>CHECKED BY DFRISIELLO</p> <p>APPROVED BY PHOSPODAR</p>	<p>DATE</p> <p>09/28/2021</p> <p>09/28/2021</p> <p>09/28/2021</p>	<p>L-com an INFINITO brand</p> <p>50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936</p>		
	<p>CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY</p> <p>COLOR VARIATIONS MAY OCCUR</p>	<p>PRODUCT DESCRIPTION</p> <p>CA ST-ST 50/125 MULTIMODE</p>			
<p>SCALE: NONE</p>		<p>SIZE A</p>	<p>CAGE CODE 43321</p>	<p>ITEM NO. FCA-M3SR-STST</p>	<p>REV. A</p>
<p>CAD FILE: FCA-M3SR-STST.SLDDRW</p>			<p>SHEET 1 OF 1</p>		