


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	2/4/22	JJOHNSTON



WIRING MAP	
MPO FIBER #	COLOR
1	BLUE
2	ORANGE
3	GREEN
4	BROWN
5	GREY
6	WHITE
7	RED
8	BLACK
9	YELLOW
10	PURPLE
11	PINK
12	AQUA
13	BLUE
14	ORANGE
15	GREEN
16	BROWN
17	GREY
18	WHITE
19	RED
20	BLACK
21	YELLOW
22	PURPLE
23	PINK
24	AQUA



PART NUMBER	LENGTH METERS [FEET]
FCA-MMS124D90P	0.5 [1.64]
FCA-MMS124D91P	1.0 [3.28]

**NOTES:**

- SC CONNECTOR ASSEMBLY POLISH TYPE: UPC
- ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

**REGULATORY COMPLIANCE:**

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5]      FRACTIONS ± 1/32 .XX = ± .02 [.5]      ANGLES ± 1° .XXX = ± .005 [.13]	APPROVALS	DATE	 an INFINITO brand	50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	DRAWN BY DMAY	1/24/22		
THIRD-ANGLE PROJECTION 	CHECKED BY DFRISIELLO	1/28/22	CATEGORY <b>FIBER OPTICS</b>	
	APPROVED BY JJOHNSTON	2/4/22	PRODUCT DESCRIPTION PATCH CORD SM OS2 24CORES MPO(MALE, STANDARD LOSS)-SC/UPC 0.9mm PVC COLOUR	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		SIZE <b>A</b>	CAGE CODE <b>43321</b>
	COLOR VARIATIONS MAY OCCUR		ITEM NO. <b>FCA-MMS124D9</b>	REV. <b>A</b>
			SCALE: NONE	CAD FILE: FCA-MMS124D9.SLDDRW
				SHEET 1 OF 1