


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	2/4/22	JJOHNSTON



PART NUMBER	LENGTH METERS [FEET]
FCA-MMS208600P	0.5 [1.64]
FCA-MMS208601P	1.0 [3.28]



WIRING MAP	
MPO FIBER #	COLOR
1	N/A
2	N/A
3	BLUE
4	ORANGE
5	GREEN
6	BROWN
7	GREY
8	WHITE
9	RED
10	BLACK
11	N/A
12	N/A

NOTES:

- LC CONNECTOR ASSEMBLY POLISH TYPE: PC
- ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13]	APPROVALS DRAWN BY DMAY CHECKED BY DFRISIELLO APPROVED BY JJOHNSTON	DATE 1/26/22 1/28/22 2/4/22	 an INFINITO® brand 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR	CATEGORY FIBER OPTICS		PRODUCT DESCRIPTION PATCH CORD MM OM3 8CORES MPO(MALE, STANDARD LOSS)-LC/PC 0.25mm PVC 8COLOUR
THIRD-ANGLE PROJECTION 	SIZE A	CAGE CODE 43321	ITEM NO. FCA-MMS20860	REV. A
SCALE: NONE		CAD FILE: FCA-MMS20860.SLDDRW		SHEET 1 OF 1