


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	05/22/2023	DMAY	PHOSPODAR



**PERFORMANCE SPECIFICATIONS:**

WAVELENGTH: 1550 nm.  
 INSERTION LOSS: ≤0.9 dB.

RETURN LOSS (APC): ≥40 dB.  
 EXTINCTION RATIO AT 23 °C: 23 dB MIN (25 dB TYP).  
 KEY ORIENTATION: SLOW AXIS.

AXIS ALIGNMENT: ±3°. PM FIBER, CONNECTOR KEY ARE ALIGNED WITH SLOW AXIS (FAST AXIS IS NOT CUT OFF).

OPERATING TEMPERATURE: -20°C TO +70°C.  
 STORAGE TEMPERATURE: -40°C TO +80°C.

FIBER TYPE: PM1550.  
 ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).  
 CABLE ASSEMBLIES TO BE TESTED FOR CONTINUITY.  
 CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:  
 EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

ITEM NUMBER	LENGTH	
	METERS	FEET
FCA-PM15FCALCA-2-01	1.0	3.28
FCA-PM15FCALCA-2-02	2.0	6.56






DIAGRAM OF END FACE

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5]   FRACTIONS ± 1/32 .XX = ±.02 [5]   ANGLES ± 1° .XXX = ±.005 [13]	APPROVALS	DATE	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	DRAWN BY DMAY	05/19/2023	
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR	CHECKED BY HBAKKE	05/22/2023	PRODUCT DESCRIPTION FIBER OPTIC PATCH CABLE, SIMPLEX POLARIZED MAINTAINING (PM), FC APC TO LC APC, 1550nm, 2mm LOOSE TUBE
THIRD-ANGLE PROJECTION 	APPROVED BY PHOSPODAR	05/22/2023	
			CAGE CODE <b>43321</b>
			ITEM NO. <b>FCA-PM15FCALCA-2</b>
			REV. <b>A</b>
			SCALE: NONE   CAD FILE: FCA-PM15FCALCA-2.SLDDRW   SHEET 1 OF 1