


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	09/25/2023	LNAGARAJ	PHOSPODAR



SPECIFICATIONS:	
FIBER TYPE/MODE	OM5 50/125um
OPERATING WAVELENGTH	850nm, 1300nm
INSERTION LOSS	≤0.2dB
RETURN LOSS	≥30dB
MINIMUM BEND RADIUS (FIBER CORE)	10mm
MINIMUM BEND RADIUS (FIBER CABLE)	10/5D (DYNAMIC/STATIC)
OPERATING TEMPERATURE	-40°C~+60°C
STORAGE TEMPERATURE	-45°C~+85°C
COMPLIANT STANDARDS	CE, RoHS, REACH and IEC

PART NUMBER	LENGTH METER [FEET]
FCA-SMPSTP-DPM5V-01	1.0 [3.28]
FCA-SMPSTP-DPM5V-05	5.0 [16.40]

- NOTES:
- ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
  - CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5]   FRACTIONS ± 1/32 .XX = ±.02 [5]   ANGLES ± 1° .XXX = ±.005 [13]	APPROVALS DRAWN BY LNAGARAJ CHECKED BY TCAHALANE APPROVED BY PHOSPODAR	DATE 09/25/2023 09/28/2023 09/29/2023	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936		
	THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR		CATEGORY FIBER OPTICS	PRODUCT DESCRIPTION FIBER OPTIC PATCH CABLE SMA TO ST DUPLEX 50/125 MULTIMODE PVC
		SIZE A	CAGE CODE 43321	ITEM NO. FCA-SMPSTP-DPM5V	REV. A
		SCALE: NONE	CAD FILE: FCA-SMPSTP-DPM5V.SLDRW	SHEET 1 OF 1	