


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	DRAWING REPLACES FOA-011-OD1	10/1/14	D.FRISIELLO



NOTES:

MATERIALS:

- SLEEVE: PHOSPHOR BRONZE
- BODY: ZINC ALLOY
- DUST CAP: ENGINEERING PLASTIC
- RIVET: COPPER

FINISH:

- BODY: NICKEL PLATE
- RIVET: TIN PLATE

ALL DIMENSIONS ARE FOR REFERENCE ONLY.

COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:

CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 >12 [305] ≤ 60 [1524] = +2 [51] / -0 >60 [1524] ≤ 120 [3048] = +4 [102] / -0 >120 [3048] ≤ 300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = \pm .2 [5.08] .XX = \pm .02 [51] .XXX = \pm .005 [1.27]	APPROVALS DRAWN BY C.McCORMICK CHECKED BY DFP APPROVED BY R.CARRICK	DATE 12/19/00 01/12/01 01/12/01	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		
PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321
		DWG. NO. FOA-011	REV. A
		SCALE: NONE	CAD FILE: FOA-011.SLDDRW
		SHEET 1 OF 1	