





THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	08/25/2023	KGLEBOVA	PHOSPODAR



MTG HOLE
1.7mm MAX THK
REF ONLY



NOTES:

1. ADAPTER SUPPLIED WITH 8 DUST CAPS INSTALLED WHICH ARE NOT SHOWN.

2. ADAPTER SHALL BE INDIVIDUALLY PACKAGED IAW L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

<p>UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]</p> <p>OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0</p> <p>ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13]</p> <p>THIRD-ANGLE PROJECTION</p>	APPROVALS	DATE	<p>50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936</p>
	DRAWN BY KGLEBOVA	08/15/2023	
	CHECKED BY DMAY	08/15/2023	
	APPROVED BY PHOSPODAR	08/15/2023	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		<p>CATEGORY</p> <p>FIBER OPTIC</p>
	COLOR VARIATIONS MAY OCCUR	<p>PRODUCT DESCRIPTION</p> <p>SN SR-SR QUAD CHANNEL (8F) ADAPTER, WITHOUT FLANGE, BLUE</p>	<p>SIZE</p> <p>A</p>
		<p>CAGE CODE</p> <p>43321</p>	<p>ITEM NO.</p> <p>FOA-SN94-01</p>
		<p>SCALE: NONE</p>	<p>CAD FILE: FOA-SN94-01.SLDDRW</p>
			<p>SHEET 1 OF 1</p>