

6

5

4

3

2

1

| | |
|----------------------|-----------------|
| FIBER TYPE | SINGLE MODE |
| CORE DIAMETER | 9 μ m |
| CLADDING DIAMETER | 125 μ m |
| CABLE (O.D.) (mm) | 2.9 * 5.8 |
| CABLE THICKNESS (mm) | 0.49 \pm 0.04 |
| CABLE MATERIAL | LSZH |
| BUFFER (O.D.) (mm) | 0.87 \pm 0.05 |
| BUFFER MATERIAL | PVC |

| | | |
|--------------------------|--------------------------------------|-----------------------|
| WAVELENGTH: | 850/1300nm FIBER TYPE | 850/1300nm MAXIMUM |
| ATTENUATION | 3.0/1.0 dB/km | 3.5/1.5 dB/km |
| OFL BANDWIDTH (MHz.km) | \geq 500/500 | |
| EFFECTIVE MODER (MHz.km) | N.A. | |
| 10G ETHERNET SX (M) | N.A. | |
| STRENGTH MEMBERS | ARAMID YARN | |
| JACKET SHRINKAGE | \leq 5%(2H BAKE AT 85°C \pm 2°C) | |

| | |
|---------------------------|-----|
| MAX. TENSILE STRENGTH (N) | |
| SHORT TERM | 200 |
| LONG TERM | 100 |

| | |
|-----------------------|----------|
| MIN. BEND RADIUS (mm) | |
| DYNAMIC | 20X DIA. |
| STATIC | 10X DIA. |

| | |
|---------------------------------|-----|
| MAX. CRUSH RESISTANCE (N/100mm) | |
| SHORT TERM | 500 |
| LONG TERM | 100 |

NOTES:


1. BULK CABLE SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.


REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

| REVISION | | | | | |
|----------|-----|-----------------|------------|------------|-----------|
| ZONE | REV | DESCRIPTION | DATE | CHANGED BY | APPROVED |
| | A | INITIAL RELEASE | 10/19/2023 | PSRINIVAS | PHOSPODAR |



| | | | | | |
|---|-----------|---|------------------|---|-------|
| UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS | |  an INFINIT@ brand Website: www.L-com.com Phone: 1.800.341.5266 1.978.682.6936 | |  INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5 | |
| TOLERANCES: .X = \pm .2 [5] FRACTIONS .XX = \pm .02 [0.5] \pm 1/32 .XXX = \pm .005 [0.13] ANGLES \pm 1° | | | | SCALE | SHEET |
| CABLE LENGTH TOLERANCES: \leq 12 [305] = \pm 1 [25] / -0 $>$ 12 [305] \leq 60 [1524] = \pm 2 [51] / -0 $>$ 60 [1524] \leq 120 [3048] = \pm 4 [102] / -0 $>$ 120 [3048] \leq 300 [7620] = \pm 6 [152] / -0 $>$ 300 [7620] = \pm 5% / -0 | | NONE | 1 OF 1 | | |
| DESCRIPTION | | | | | |
| ROUND DUPLEX OPTICAL CABLE, 9/125 SINGLE MODE, LSZH RATED, 3.0mm, 500 METERS | | | | | |
| SIZE | CAGE CODE | DRAWN BY | ITEM NO. | REV | |
| A | 43321 | PSRINIVAS | FOB-2F3DSMZ-500M | A | |

6

5

4

3

2

1