8		7	6		5	+	4		3		2		1
	CONTAINED IN THIS	S DRAWING IS THE SC DUCTION IN PART OR W	DLE					REV		DESCE	REVISIONS	DATE	APPROVED
THOUT THE WRITT	EN PERMISSION OF L-	COM, INC. IS PROHIBITE	ED.						ITIAL RELEASE	DESCI		05/13/2	
FIBER CO			6		1								
FIBER TYP			MULTIMODE - ON		1								
CORE DIA				AI, KIJEK	-								
	G DIAMETER		62.5 µm		-								
	G DIAMETER		125 µm		-								
BUFFER			0.85 ±0.05										
			850/1300nm	850/13	300nm								
WAVELEN	iGTH:		TYPICAL	MAX									
ATTENUA			3.0/1.0 dB/km	3.5/1.5	UD/KIII								
MAY TEN	SILE STRENGTH	(N)											
SHORT TER		(14)	320										
LONG TER			160							_	Riser Rated Ja	cket	
LONG IER	171		160								Color: Orange		
							Ø5.0 —			×	-		
MIN. BENI	D RADIUS (mm	i)						\mathbf{N}					
DYNAMIC		,	15X DIA.						(\bigcirc)	$\langle \rangle$			
STATIC			7.5X DIA.						$) \bigcirc \bigcirc$		-Aramid Yarn		
									\mathcal{I}	11	Strength Men	nber	
MAX. CR								$\setminus \setminus (\bigcirc$)/ /			
RESISTAN	CE (N/100mm))							(\bigcirc)				
SHORT TE	RM		1000						<u> </u>				
LONG TEP	2M		300							\frown			
<u>.</u>										\sim	-Tight Buffered		
							AL	L DIMENSI	ons in mm	, DRAWIN	IG NOT TO SC	ALE	
							ERWISE SPECIFIED.					50 High Street, V	Aloct Mill
							ARE IN INCHES [mm]	APPROVAL	S DATE		COM	North Andover,	MA 01845 U
NOTES:							LENGTH TOLERANCE 2 [305] = +1 [25] / -0		05/13/2022		n INFINIT [®] brand	Phone: 1.800.34 1.978.68	41.5266 32.6936
						>12 [305] ≤6	D [1524] = +2 [51] / -0 D [3048] = +4 [102] / -0	CHECKED BY	05/13/2022	CATEGORY			
		-	PACKAGED IN			>120 [3048] ≤30	0 [7620] = +6 [152] / -0	APPROVED BY	05/13/2022	_	FIBER	R OPTIC	
ACCOR	DANCE WITH	L-COM SPECIF	ICATION PS-0031.) [7620] = +5% / -0 \sional tolerance	PHOSPODAR		PRODUCT DE	SCRIPTION		
						.X = ± .2 [5] .XX = ± .02 [.5]	FRACTIONS	UNDIMENS	ATION DETAILS OF SIONED FEATURES	INE	DOOR MULTI-I	FIBER DISTRIE	BUTION
	RY COMPLIAN	NCE:				.XXX = ± .005 [.	13] ANGLES ± 1°	M	AY VARY		<u>3LE, 6 FIBER, 6</u>	2.5/125 OM	
REGULATO						THIRD-ANC	GLE PROJECTION	COLOF	r variations		AGE CODE ITEM NO.		R
	IRECTIVE (MO	ST RECENT RFI	EASED VERSION			-	_				42201 Fr		
	IRECTIVE (MO	INST RECENT REL	eased version)			(()) -[-]		YOCCUR		43321 FC	B-MFD-6FM1	R-M