	REVISIONS					
REV	DESCRIPTION	DATE	APPROVAL			
Α	DRAWING REPLACES FOB625S-M-OD1	6/25/14	D. DESJARDIN			

TABLE						
FOB625S-M	62.5/125 MICRON GRADED INDEX, MULTIMODE OFNR RATED SIMPLEX CABLES WITH PVC JACKETS.					
FOB500S-M	50/125 MICRON GRADED INDEX, MULTIMODE OFNR RATED SIMPLEX CABLES WITH PVC JACKETS.					
FOBSNGS-M	9/125 MICRON GRADED INDEX, SINGLE MODE OFNR RATED SIMPLEX CABLES WITH PVC JACKETS.					

GENERAL CHARACTERISTICS FOR RISER RATED (OFNR) SIMPLEX FIBER CABLES

MINIMUM BEND RADIUS: UNDER INSTALLATION: 3.0CM UNDER LONG-TERM: 4.5CM

OPERATING TEMPERATURE: -20°C TO +70°C STORAGE TEMPERATURE: -40°C TO +70°C

MAX. TENSILE LOAD LBF: SHORT TERM 134LBF LONG TERM 44LBF

OPTICAL PERFORMANCE: MAX ATTENUATION DB/KM

850NM 3.5DB 1300NM 1.5DB

1310NM 1.0DB 1550NM 1.0DB

BANDWIDTH: MHZ/KM 850NM 200 MHZ/KM (62.5/125) 1300NM 500 MHZ/KM (62.5/125)

850NM 500 MHZ/KM (50/125) 1300NM 500 MHZ/KM (50/125)

1310NM ~100 TERAHERTZ 1550NM ~100 TERAHERTZ

THESE SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT PRIOR NOTIFICATION.

PACKAGING:

LESS THAN 50 METERS (164 FT): INDIVIDUALLY PACKAGE IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

50 METERS (164 FT) OR MORE: TO BE SPOOLED WITH 5' PIGTAILS

	UNLESS OTHERWISE SPECIFIED.	APPROVALS	DATE		_	_	Global	45 BEECHWOOD	DDIVE
	DIMENSIONS ARE IN INCHES [mm]	MCCORMICK	12/17/01	Ŀ			Connectivity	NORTH ANDOVE	R, MA
	OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0	CHECKED BY D.PARHAM	12/17/01				Connectivity	01845	
	>12 [305] - 60 [1524] = +2 [51] / -0 >60 [1524] - 120 [3048] = +4 [102] / -0 >120 [3048] - 300 [7620] = +6 [152] / -0	APPROVED BY R.CARRICK	12/17/01	FIBER OPTICS					
	>300[7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES:	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUCT DESCRIPTION CBL FIBER SMPLX OFNR					
Р	ROJECTION (+)	COLOR VARIATIONS MAY OCCUR		SIZE		м NO. 321	DWG. NO. FOB625S	-M	A REV.
	9 —			SCALE:	1:1	CAD F	FILE: FOB625S-M.SLDDRW	SHEET	1 OF 1