


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	06/03/2020	PHOSPODAR

FIBER TYPE	FIBER CABLE JACKET DIAMETER OPTIONS WITHOUT DUST CAP			
	4.5-4.9mm	5.3-5.8mm	5.8-6.2mm	6.8-7.2mm
SC/PC MMF	FOC-IPSCMM-48N	FOC-IPSCMM-50N	FOC-IPSCMM-60N	FOC-IPSCMM-70N
SC/UPC SMF	FOC-IPSCSM-48N	FOC-IPSCSM-50N	FOC-IPSCSM-60N	FOC-IPSCSM-70N
SC/APC SMF	FOC-IPSCSA-48N	FOC-IPSCSA-50N	FOC-IPSCSA-60N	FOC-IPSCSA-70N

FIBER TYPE	FIBER CABLE JACKET DIAMETER OPTIONS WITH DUST CAP			
	4.5-4.9mm	5.3-5.8mm	5.8-6.2mm	6.8-7.2mm
SC/PC MMF	FOC-IPSCMM-48D	FOC-IPSCMM-50D	FOC-IPSCMM-60D	FOC-IPSCMM-70D
SC/UPC SMF	FOC-IPSCSM-48D	FOC-IPSCSM-50D	FOC-IPSCSM-60D	FOC-IPSCSM-70D
SC/APC SMF	FOC-IPSCSA-48D	FOC-IPSCSA-50D	FOC-IPSCSA-60D	FOC-IPSCSA-70D



FOC-IPSC**-**D ITEM NUMBERS WITH DUST CAP





FOC-IPSC**-**N ITEM NUMBERS WITHOUT DUST CAP

NOTES:

1. ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13]	APPROVALS	DATE	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	DRAWN BY DZINN	06/03/2020	
THIRD-ANGLE PROJECTION 	APPROVED BY PHOSPODAR	06/03/2020	CATEGORY FIBER OPTIC
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR	PRODUCT DESCRIPTION IP68 RATED SC CONNECTOR, 4.5-7.2mm	SIZE A	CAGE CODE 43321
	ITEM NO. FOC-IPSC	SCALE: NONE	CAD FILE: FOC-IPSC.SLDDRW
			SHEET 1 OF 1