




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	4/5/12	D.GRIFFIN
B	ECN 8626: ADDED O-RING AND FERRULE	2/1/17	D.FRISIELLO
C	ECN 8941: ADDED NOTE TO O-RING AND FERRULE	9/26/17	D.FRISIELLO

MODEL NUMBER	USED WITH
FOC-RSTMMLN1	1.9 - 2.0mm
FOC-RSTMMLN2	2.0 - 2.5mm
FOC-RSTMMLN3 *	2.5 - 3.0mm



NOTES:
 MATERIAL: NICKEL PLATED BRASS.
 CONNECTOR ASSEMBLY POLISH TYPE: PC.
 MODEL IS LOCKING STYLE, MULTIMODE.
 STRIP FIBER CABLE TO MIL-STD-2042-5B. STRIP DIMENSIONS ARE +/- 1mm.
 DUST CAP IS INSTALLED FOR SHIPMENT.

"" DENOTES O-RING AND CRIMP FERRULE ONLY PRESENT ON FOC-RSTMMLN3.

COMPONENTS COME UNASSEMBLED AND SHALL BE INDIVIDUALLY PACKAGED IN A POLY BAG.

REGULATORY COMPLIANCE:
 CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE	 50 HIGH STREET NORTH ANDOVER, MA 01845			
	DRAWN BY D.FRISIELLO	3/2/12			CATEGORY FIBER OPTICS	
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [51] .XXX = ±.005 [1.27]	CHECKED BY D.GUITADAURO	3/2/12	PRODUCT DESCRIPTION ST RGD MM LOCKING NPB			
	APPROVED BY D.GALLAGHER	3/2/12			<table border="1"> <tr> <td>SIZE A</td> <td>FSCM NO. 43321</td> <td>DWG. NO. FOC-RSTMMLN</td> <td>REV. C</td> </tr> </table>	SIZE A
SIZE A	FSCM NO. 43321	DWG. NO. FOC-RSTMMLN	REV. C			
PROJECTION 	COLOR VARIATIONS MAY OCCUR	SCALE: NONE	CAD FILE: FOC-RSTMMLN.SLDDRW	SHEET 1 OF 1		