


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	01/11/2022	PHOSPODAR





ASSY CONNECTIVITY	
AARC 2 CORE SKT	LC/UPC
PIN1	B
PIN2	A

ITEM NO.	LENGTH	
	METER	FEET
FOC02A3027101M	1.0	3.28
FOC02A3027102M	2.0	6.56
FOC02A3027105M	5.0	16.40
FOC02A3027110M	10.0	32.81
FOC02A3027115M	15.0	49.21

**NOTES:**

1. LC CONNECTOR POLISH TYPE: UPC.
2. AARC CONNECTOR COMES WITH A DUST CAP INSTALLED.
3. LC CONNECTORS COM WITH DUST PLUG INSTALLED (NOT SHOWN)
4. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

**REGULATORY COMPLIANCE:**  
EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5]   FRACTIONS ± 1/32 .XX = ± .02 [5]   ANGLES ± 1° .XXX = ± .005 [13]	APPROVALS DRAWN BY: DZINN CHECKED BY: DFRISIELLO APPROVED BY: PHOSPODAR	DATE 01/18/2022 01/18/2022 01/18/2022	 an INFINITO brand 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR	PRODUCT DESCRIPTION Fiber Optic Outdoor patch cable, Duplex SMF[G.657.A2], 2 core AARC(Socket) to dual clipped LC/UPC with Armored 7.0mm LSZH jacket
SIZE: <b>A</b>   CAGE CODE: <b>43321</b>   ITEM NO.: FOC02A30271   REV.: <b>A</b>			