


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	08-02-2021	PHOSPODAR




PART NUMBER	DESCRIPTION
FOCASE2K1UPC02-1	E2000 UPC 2mm FIBER OPTIC PIGTAIL 1M
FOCASE2K1UPC02-2	E2000 UPC 2mm FIBER OPTIC PIGTAIL 2M
FOCASE2K1UPC02-5	E2000 UPC 2mm FIBER OPTIC PIGTAIL 5M
FOCASE2K1UPC02-10	E2000 UPC 2mm FIBER OPTIC PIGTAIL 10M
FOCASE2K1UPC02-15	E2000 UPC 2mm FIBER OPTIC PIGTAIL 15M

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]

OVERALL CABLE LENGTH TOLERANCE:  
 ≤12 [305] = +1 [25] / -0  
 >12 [305] ≤60 [1524] = +2 [51] / -0  
 >60 [1524] ≤120 [3048] = +4 [102] / -0  
 >120 [3048] ≤300 [7620] = +6 [152] / -0  
 >300 [7620] = +5% / -0

ALL OTHER DIMENSIONAL TOLERANCES:  
 .X = ± .2 [5] | FRACTIONS ± 1/32  
 .XX = ± .02 [.5] | ANGLES ± 1°  
 .XXX = ± .005 [.13]

THIRD-ANGLE PROJECTION



APPROVALS	DATE
DRAWN BY MVEERAPPAN	08-02-2021
CHECKED BY GIBACETA	08-02-2021
APPROVED BY PHOSPODAR	08-02-2021

**L-com**  
an INFINITO brand

50 High Street, West Mill,  
North Andover, MA 01845 USA.  
Phone: 1.800.341.5266  
1.978.682.6936

CATEGORY  
**FIBER OPTICS**

PRODUCT DESCRIPTION  
**E2000 UPC 2mm fiber optic pigtail**

SIZE	CAGE CODE	ITEM NO.	REV.
<b>A</b>	<b>43321</b>	<b>FOCASE2K1UPC02</b>	<b>A</b>

SCALE: NONE | CAD FILE: FOCASE2K1UPC02.SLDDRW | SHEET 1 OF 1