


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	01/18/2022	PHOSPODAR



ASSY CONNECTIVITY	
AARC 4 CORE SKT	AARC 4 CORE SKT
PIN1	PIN4
PIN2	PIN3
PIN3	PIN2
PIN4	PIN1

ITEM NO.	LENGTH	
	METER	FEET
FOCB026047N01M	1.0	3.28
FOCB026047N02M	2.0	6.56
FOCB026047N05M	5.0	16.40
FOCB026047N10M	10.0	32.81
FOCB026047N15M	15.0	49.21

NOTES:

1. AARC CONNECTOR COMES WITH DUST CAP INSTALLED.
2. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [5] ANGLES ± 1° .XXX = ± .005 [13]	APPROVALS	DATE		50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	DRAWN BY DZINN	01/18/2022		
THIRD-ANGLE PROJECTION 	CHECKED BY DFRISIELLO	01/18/2022	CATEGORY	
	APPROVED BY PHOSPODAR	01/18/2022	FIBER OPTIC	
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	PRODUCT DESCRIPTION		Fiber Optic Outdoor patch cable, 4 fiber MMF(OM3), 4 core AARC(Socket) to 4 core AARC(Socket) with 7.0mm LSZH jacket	
COLOR VARIATIONS MAY OCCUR	SIZE A	CAGE CODE 43321	ITEM NO. FOCB026047N	REV. A
SCALE: NONE		CAD FILE: FOCB026047N.SLDDRW		SHEET 1 OF 1