


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	01/18/2022	PHOSPODAR



H-OPTIC CONNECTOR HOUSING  
SC/APC CONNECTOR

H-OPTIC CONNECTOR HOUSING  
SC/APC CONNECTOR

5mm G657A2 SIMPLEX,  
LSZH, BLACK



ITEM NO.	LENGTH	
	METER	FEET
FOCB033015N01M	1.0	3.28
FOCB033015N02M	2.0	6.56
FOCB033015N05M	5.0	16.40
FOCB033015N10M	10.0	32.81
FOCB033015N15M	15.0	49.21

**NOTES:**

1. SC CONNECTOR POLISH TYPE: APC.
2. H-OPTIC HOUSING COMES WITH DUST COVER INSTALLED.
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

**REGULATORY COMPLIANCE:**

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]  OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0  ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5]      FRACTIONS ± 1/32 .XX = ± .02 [.5]      ANGLES ± 1° .XXX = ± .005 [.13]	APPROVALS DRAWN BY DZINN CHECKED BY DFRISIELLO APPROVED BY PHOSPODAR	DATE 01/18/22 01/18/22 01/18/22	 an INFINITO brand	50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY  COLOR VARIATIONS MAY OCCUR	PRODUCT DESCRIPTION Fiber Optic Outdoor patch cable, Simplex SMF(G.657.A2), H-Optic SC/APC to H-Optic SC/APC with 5.0mm LSZH jacket	CATEGORY <b>FIBER OPTIC</b>
SCALE: NONE		CAGE CODE <b>43321</b>	ITEM NO. <b>FOCB033015N</b>	REV. <b>A</b>
CAD FILE: FOCB033015N.SLDDRW			SHEET 1 OF 1	