


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION					
ZONE	REV.	DESCRIPTION	DATE	CHANGED BY	APPROVED BY
	A	INITIAL RELEASE	08/10/2023	BPUCHASKI	PHOSPODAR




LENGTH	TOLERANCE
L < 1M	+50mm / -0
1M ≤ L ≤ 10M	+100mm / -0
L > 10M	+1% L / -0

CABLE SPECIFICATIONS	
ITEM	SPECIFICATION
JACKET DIAMETER	10.5 mm ±0.5
JACKET COLOR /MATERIAL	BLACK / LSZH
MIN. BEND RAD. (D: CABLE DIAM.)	10D mm STATIC 20D mm DYNAMIC
ATTENUATION	≤0.4 dB/km@1310nm, ≤0.3 dB/km@1550nm
SHORT TERM TENSILE	500 N
LONG TERM TENSILE	200 N
CRUSH RESISTANCE	1000 N/100mm
OPERATION TEMP.	-40~+70 °C
INSTALLATION TEMP.	-20~+60 °C
STORAGE TEMP.	-40~+70 °C
STRENGTH MEMBER	ARAMID YARN
INNER JACKET MATERIAL	LSZH
INNER JACKET COLOR	BLACK
INNER JACKET DIAM.	2.6 mm ±0.2

OPTICAL SPECIFICATIONS	
FIBER TYPE	MULTI MODE
POLISH TYPE	LCUPC
INSERTION LOSS	≤ 0.3dB
TEST WAVELENGTH	850nm & 1300nm

ENDFACE GEOMETRY	
SPECIFICATION TYPE	LCUPC
RADIUS OF CURVATURE	7mm TO 25mm
APEX OFFSET	< 50 um
FIBER HEIGHT	-50nm TO +50nm



CABLE PROFILE VIEW

NOTES:

- ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN)
  - CABLE ASSEMBLY LENGTH DETERMINED BY P/N AS ILLUSTRATED:  
FOCM4IPHLCPHLC-XXX (-XXX = OAL IN METERS)
- REGULATORY COMPLIANCE:  
EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5]   FRACTIONS ± 1/32 .XX = ± .02 [0.5]   ANGLES ± 1° .XXX = ± .005 [0.13]	APPROVALS DRAWN BY BPUCHASKI CHECKED BY REVANGELIS APPROVED BY PHOSPODAR	DATE 08/10/2023 08/10/2023 08/10/2023	50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR	CATEGORY <b>FIBER OPTICS</b>		PRODUCT DESCRIPTION <b>IP68 HYBRID LC/UPC TO IP68 HYBRID LC/UPC, 10.5mm OM4, CABLE ASSEMBLY</b>
THIRD-ANGLE PROJECTION 	SIZE <b>A</b>	CAGE CODE <b>43321</b>	ITEM NO. <b>FOCM4IPHLCPHLC-XXX</b>	REV. <b>A</b>
SCALE: NONE		CAD FILE: FOCM4IPHLCPHLC.SLDDRW		SHEET 1 OF 1