


LENGTH	
LENGTH (L) METER [FEET]	TOLERANCE MM [INCHES]
5 [16.40]	+50/-0 [+1.97/0]
10 [32.81]	+100/-0 [+3.94/0]
20 [65.62]	+1%*L/-0
30 [98.43]	+1%*L/-0

OPTICAL SPECIFICATION	
FIBER TYPE	SINGLE MODE
CONNECTOR TYPE	IP-MPO/APC
INSERTION LOSS	≤ 0.75dB
RETURN LOSS	≥ 55dB
TEST WAVE LENGTH	1310 & 1550nm


REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	B	ECO-13297	02/08/2024	DZINN	PHOSPODAR



- NOTES:
1. MPO CONNECTOR ASSEMBLY POLISH TYPE: APC
  2. MPO POLARITY: TIA METHOD B.
  3. ALL CONNECTORS INCLUDE PROTECTIVE DUST CAPS.
  4. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IAW L-COM SPECIFICATION PS-0031.
- REGULATORY COMPLIANCE:  
EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [ ] ARE MILLIMETERS	
TOLERANCES:	
.X = ±.2 [5]	FRACTIONS ± 1/32
.XX = ±.02 [0.5]	ANGLES ± 1°
.XXX = ±.005 [0.13]	
CABLE LENGTH TOLERANCES:	
≤12 [305] = +1 [25] / -0	
>12 [305] ≤ 60 [1524] = +2 [51] / -0	
>60 [1524] ≤ 120 [3048] = +4 [102] / -0	
>120 [3048] ≤ 300 [7620] = +6 [152] / -0	
>300 [7620] = +5% / -0	
ALL DIMENSIONS ARE FOR REFERENCE ONLY AND SUBJECT TO CHANGE WITHOUT NOTICE UN-DIMENSIONED/NON-CRITICAL FEATURES MAY VARY IN SIZE AND LOCATION COLORS MAY VARY	



**an INFINIT@ brand**

Website: [www.L-com.com](http://www.L-com.com)  
Phone: 1.800.341.5266 | 1.978.682.6936

INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5 SCALE: NONE    SHEET: 1 OF 1				
DESCRIPTION <b>IP68 OUTDOOR CABLE ASSY, 5MM OD, OS2, MPO/APC MALE 24F TO MPO/APC MALE 24F, TYPE B</b>				
SIZE: A	CAGE CODE: 43321	DRAWN BY: DZINN	ITEM NO.: FOC520DMPMB24	REV: B