


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	RELEASED FOR PRODUCTION	09/19/11	DFP
B	ECN 7543: REVISED PICTORIALY, FORMAT, ADDED REF. DIMS., ROHS	8/7/14	D.FRISIELLO
C	ECN 8342: REVISED REFERENCE DIMENSIONS	5/23/16	D.FRISIELLO



NOTES:

1. LANYARDS ARE PACKAGED 25 PIECES PER BAG IN ACCORDANCE L-COM SPECIFICATION PS-0031.
 2. MATERIAL: CLEAR PLASTIC
- REGULATORY COMPLIANCE:**
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE			50 HIGH STREET NORTH ANDOVER, MA 01845	
	DRAWN BY D. PARHAM	09/19/2011			CATEGORY	FIBER OPTICS
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [1.51] .XXX = ±.005 [1.13]	CHECKED BY D. GUITADAURO	09/19/2011	PRODUCT DESCRIPTION DUST CAP WITH LANYARD 2.5MM			
	APPROVED BY S. SMITH	09/19/2011				
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. FODC-LANYARD	REV. C
			SCALE: NONE	CAD FILE: FODC-LANYARD.SLDDRW	SHEET 1 OF 1	