


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	DRAWING REPLACES FODFC50-SC-01-0D1	9/25/14	D. CASTRO



50/125 DUPLEX OM2 ONFR (RISER) ZIPCORD
O.D. 3mm, COLOR: ORANGE

PART NUMBER	LENGTH METERS [FEET]
FODFC50-SC-01	1.0 [3.28]
FODFC50-SC-02	2.0 [6.56]
FODFC50-SC-03	3.0 [9.84]
FODFC50-SC-04	4.0 [13.12]
FODFC50-SC-05	5.0 [16.40]

NOTES:

1. FC CONNECTOR ASSEMBLY POLISH TYPE: PC
SC CONNECTOR ASSEMBLY POLISH TYPE: PC
2. ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY C.MCCORMICK	01/07/2004		CATEGORY
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [5.1] .XXX = ±.005 [1.3]	CHECKED BY D.PARHAM	01/07/2004	PRODUCT DESCRIPTION	
PROJECTION 	APPROVED BY R.CARRICK	01/07/2004	CA FC-SC 50/125 DUPLEX	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		SIZE A	FSCM NO. 43321
	COLOR VARIATIONS MAY OCCUR		DWG. NO. FODFC50-SC	REV. A
			SCALE: NONE	CAD FILE: FODFC50-SC.SLDDRW
				SHEET 1 OF 1