


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	12/16/05	MCCORMICK
B	ECN4773: ADDED ROHS STAMP. UPDATED FORMAT.	05/24/10	DFP
C	ECN 6019: REVISED FEET LENGTHS	3/8/12	D.FRISIELLO





MODEL NUMBER	LENGTH	
	METERS	FEET
FODLC-10G-01	1.0	3.28
FODLC-10G-02	2.0	6.56
FODLC-10G-03	3.0	9.84
FODLC-10G-04	4.0	13.12
FODLC-10G-05	5.0	16.41

RoHS Compliant ✓

NOTES:

1. LC CONNECTOR ASSEMBLY POLISH TYPE: PC.
2. ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
3. CABLE SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 >12 [305] ≤ 60 [1524] = +2 [51] / -0 >60 [1524] ≤ 120 [3048] = +4 [102] / -0 >120 [3048] ≤ 300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	APPROVALS DRAWN BY C.MCCORMICK CHECKED BY M.LAHEY APPROVED BY D.PARHAM	DATE 12/16/2005 12/16/2005 12/16/2005	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY			CATEGORY FIBER OPTICS
	PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321
	SCALE: NONE		DWG. NO. FODLC-10G	REV. C
CAD FILE: FODLC-10G.SLDDRW			SHEET 1 OF 1	