


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

RoHS Compliant ✓

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	11/12/07	D.FRISIELLO
B	ECN3211: ADDED ORANGE CABLES	02/29/08	D.PARHAM



PART NO.	COLOR	LENGTH		PART NO.	COLOR	LENGTH		PART NO.	COLOR	LENGTH	
		METERS	FEET			METERS	FEET			METERS	FEET
FODLC-RD-01	RED	1	3.28	FODLC-BL-01	BLUE	1	3.28	FODLC-OR-01	ORANGE	1	3.28
FODLC-RD-02	RED	2	6.56	FODLC-BL-02	BLUE	2	6.56	FODLC-OR-02	ORANGE	2	6.56
FODLC-RD-03	RED	3	9.84	FODLC-BL-03	BLUE	3	9.84	FODLC-OR-03	ORANGE	3	9.84
FODLC-RD-04	RED	4	13.12	FODLC-BL-04	BLUE	4	13.12	FODLC-OR-04	ORANGE	4	13.12
FODLC-RD-05	RED	5	16.40	FODLC-BL-05	BLUE	5	16.40	FODLC-OR-05	ORANGE	5	16.40
FODLC-RD-10	RED	10	32.81	FODLC-BL-10	BLUE	10	32.81	FODLC-OR-10	ORANGE	10	32.81
FODLC-RD-15	RED	15	49.22	FODLC-BL-15	BLUE	15	49.22	FODLC-OR-15	ORANGE	15	49.22
FODLC-GR-01	GREEN	1	3.28	FODLC-YL-01	YELLOW	1	3.28				
FODLC-GR-02	GREEN	2	6.56	FODLC-YL-02	YELLOW	2	6.56				
FODLC-GR-03	GREEN	3	9.84	FODLC-YL-03	YELLOW	3	9.84				
FODLC-GR-04	GREEN	4	13.12	FODLC-YL-04	YELLOW	4	13.12				
FODLC-GR-05	GREEN	5	16.40	FODLC-YL-05	YELLOW	5	16.40				
FODLC-GR-10	GREEN	10	32.81	FODLC-YL-10	YELLOW	10	32.81				
FODLC-GR-15	GREEN	15	49.22	FODLC-YL-15	YELLOW	15	49.22				

NOTES:

CABLE CHARACTERISTICS:
62.5/125 DUPLEX FIBER ZIPCORD.
JACKET RATING: PVC, OFNR.
JACKET COLOR: SEE CHART.
CABLE O.D: 3.0 mm.

TESTING:
DOUBLE ENDED INSERTION LOSS TEST. CABLES WITH GREATER THAN 1.0 dB OF LOSS ARE REJECTED.

CONNECTOR POLISH: THIS ASSEMBLY UTILIZES A PC POLISH.

MISCELLANEOUS:
OPERATING TEMPERATURE: -20° C TO +70° C.
CABLE ASSEMBLY TO SHIP WITH DUST CAPS INSTALLED. (NOT SHOWN)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES (mm) OVERALL CABLE LENGTH TOLERANCE: $\leq 12 (305) = +1 (25) / -0$ $> 12 (305) - 60 (1524) = +2 (51) / -0$ $> 60 (1524) - 120 (3048) = +4 (102) / -0$ $> 120 (3048) - 300 (7620) = +6 (152) / -0$ $> 300 (7620) = +5\% / -0\%$ ALL OTHER DIMENSIONAL TOLERANCES: .X = .3 .XX = .15 PROJECTION 	APPROVALS DRAWN BY D.FRISIELLO CHECKED BY D.PARHAM APPROVED BY P.McNEIL	DATE 11/12/07 11/12/07 11/12/07	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845			
	CATEGORY FIBER OPTICS			PRODUCT DESCRIPTION 62.5/125LC-LC DPLX ASSEMBLY		
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR		SIZE A		FSCM NO. 43321	DWG. NO. FODLC-COLOR
	REF		SCALE: NONE CAD FILE: FODLC-COLOR.SLDDRW		SHEET 1 OF 1	

D
C
B
A

D
C
B
A

8 7 6 5 4 3 2 1

8 7 6 5 4 3 2 1