


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	DRAWING REPLACES FODPMT-LC-1-OD1	10/6/14	D. CASTRO



PART NUMBER	LENGTH METERS [FEET]
FODPMT-LC-01	1.0 [3.28]
FODPMT-LC-02	2.0 [6.56]
FODPMT-LC-03	3.0 [9.84]
FODPMT-LC-04	4.0 [13.12]
FODPMT-LC-05	5.0 [16.40]

- NOTES:**
- CONNECTOR ASSEMBLY POLISH TYPE: PC
 - ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
 - CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY C.MCCORMICK	12/03/2003		
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [1.51] .XXX = ±.005 [1.13]	CHECKED BY D.PARHAM	12/03/2003	PRODUCT DESCRIPTION	
	APPROVED BY R.CARRICK	12/03/2003	CA MTRJ-LC 62.5/125 PLEN	
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321
			DWG. NO. FODPMT-LC	REV. A
			SCALE: NONE	CAD FILE: FODPMT-LC.SLDDRW
				SHEET 1 OF 1