


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	DRAWING REPLACES FODSC-10G-01-OD1	10/6/14	D. CASTRO



PART NUMBER	LENGTH METERS [FEET]
FODSC-10G-01	1.0 [3.28]
FODSC-10G-02	2.0 [6.56]
FODSC-10G-03	3.0 [9.84]
FODSC-10G-04	4.0 [13.12]
FODSC-10G-05	5.0 [16.40]

**NOTES:**

1. SC CONNECTOR ASSEMBLY POLISH TYPE: PC
2. ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

**REGULATORY COMPLIANCE:**  
CE2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: $\leq 12$ [305] = +1 [25] / -0 $> 12$ [305] $\leq 60$ [1524] = +2 [51] / -0 $> 60$ [1524] $\leq 120$ [3048] = +4 [102] / -0 $> 120$ [3048] $\leq 300$ [7620] = +6 [152] / -0 $> 300$ [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [5.1] .XXX = ± .005 [1.3]	APPROVALS DRAWN BY C.MCCORMICK CHECKED BY M.LAHEY APPROVED BY D.PARHAM	DATE 12/16/2005 12/16/2005 12/16/2005	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR	CATEGORY FIBER OPTICS		PRODUCT DESCRIPTION SC-SC 50/125 10G DPLEX OFNR
PROJECTION 	SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. FODSC-10G	REV. <b>A</b>
SCALE: NONE		CAD FILE: FODSC-10G.SLDDRW		SHEET 1 OF 1