


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	DRAWING REPLACES FODSC50-01-OD1	10/8/14	D. CASTRO





PART NUMBER	LENGTH METERS [FEET]
FODSC50-01	1.0 [3.3]
FODSC50-02	2.0 [6.6]
FODSC50-03	3.0 [9.8]
FODSC50-04	4.0 [13.1]
FODSC50-05	5.0 [16.4]
FODSC50-10	10.0 [32.8]
FODSC50-15	15.0 [49.2]
FODSC50-20	20.0 [65.6]
FODSC50-25	25.0 [82.0]
FODSC50-30	30.0 [98.4]
FODSC50-35	35.0 [114.8]
FODSC50-40	40.0 [131.2]
FODSC50-45	45.0 [147.6]
FODSC50-50	50.0 [164.0]
FODSC50-75	75.0 [246.1]
FODSC50-100	100.0 [328.1]
FODSC50-125	125.0 [410.1]
FODSC50-150	150.0 [492.1]

NOTES:

- SC CONNECTOR ASSEMBLY POLISH TYPE: PC
- ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
- PACKAGING:
LESS THAN 50 METERS (164 FT): INDIVIDUALLY PACKAGE EACH ASSEMBLY IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.
50 METERS (164 FT) OR MORE: TO BE SPOOLED

REGULATORY COMPLIANCE:
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845			
	DRAWN BY RON CARRICK	8/16/2000		CATEGORY FIBER OPTICS		
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [5.1] .XXX = ±.005 [1.3]	CHECKED BY ENG	8/16/2000	PRODUCT DESCRIPTION CA SC-SC 50/125 DUPLEX			
	APPROVED BY AFC	8/18/2000		<table border="1"> <tr> <td>SIZE A</td> <td>FSCM NO. 43321</td> <td>DWG. NO. FODSC50</td> <td>REV. A</td> </tr> </table>	SIZE A	FSCM NO. 43321
SIZE A	FSCM NO. 43321	DWG. NO. FODSC50	REV. A			
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SCALE: NONE CAD FILE: FODSC50.SLDDRW SHEET 1 OF 1			