


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	DRAWING REPLACES FODSMI-01-OD1	10/8/14	D. CASTRO



PART NUMBER	METERS [FEET]
FODSMI-01	1.0 [3.28]
FODSMI-03	3.0 [9.84]
FODSMI-05	5.0 [16.4]
FODSMI-10	10.0 [32.8]
FODSMI-20	20.0 [65.6]

NOTES:

- CONNECTOR ASSEMBLY POLISH TYPE: PC
- ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 > 12 [305] ≤ 60 [1524] = +2 [51] / -0 > 60 [1524] ≤ 120 [3048] = +4 [102] / -0 > 120 [3048] ≤ 300 [7620] = +6 [152] / -0 > 300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [51] .XXX = ± .005 [1.27]	APPROVALS DRAWN BY C.MCCORMICK	DATE 04/28/2006	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845								
	CHECKED BY D.PARHAM	DATE 04/28/2006		CATEGORY FIBER OPTICS							
APPROVED BY J.KIEZULAS	DATE 04/28/2006	PRODUCT DESCRIPTION CBL SMI-SMI DPX POF									
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	<table border="1"> <tr> <td>SIZE</td> <td>FSCM NO.</td> <td>DWG. NO.</td> <td>REV.</td> </tr> <tr> <td>A</td> <td>43321</td> <td>FODSMI</td> <td>A</td> </tr> </table>	SIZE	FSCM NO.	DWG. NO.	REV.	A	43321	FODSMI	A
SIZE	FSCM NO.	DWG. NO.	REV.								
A	43321	FODSMI	A								
SCALE: NONE		CAD FILE: FODSMI.SLDDRW									
			SHEET 1 OF 1								