


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	11/12/07	D.FRISIELLO
B	ECN 7306: ADD COLOR ORANGE, SHEET 2, REVISE ROHS NOTE, FORMAT	2/21/14	D.FRISIELLO



NOTES:



CABLE CHARACTERISTICS:
 62.5/125 DUPLEX FIBER ZIPCORDER.
 JACKET RATING: PVC, OFNR.
 JACKET COLOR: SEE CHART, SHEET 2 OF 2
 CABLE O.D: 3.0 mm.

TESTING:
 DOUBLE ENDED INSERTION LOSS TEST. CABLES WITH GREATER THAN 1.0 dB OF LOSS ARE REJECTED.

CONNECTOR POLISH: THIS ASSEMBLY UTILIZES A PC POLISH.

MISCELLANEOUS:
 OPERATING TEMPERATURE: -20° C TO +70° C.
 CABLE ASSEMBLY TO SHIP WITH DUST CAPS INSTALLED. (NOT SHOWN).
 CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.


REGULATORY COMPLIANCE:
 CE2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [51] .XXX = ±.005 [1.27]	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845			
	DRAWN BY D.FRISIELLO	11/12/07		CATEGORY FIBER OPTICS		
	CHECKED BY D.PARHAM	11/12/07	PRODUCT DESCRIPTION SC-SC DPLX ASSEMBLY			
	APPROVED BY P.McNEIL	11/12/07		<table border="1"> <tr> <td>SIZE A</td> <td>FSCM NO. 43321</td> <td>DWG. NO. FODST-COLOR</td> <td>REV. B</td> </tr> </table>	SIZE A	FSCM NO. 43321
SIZE A	FSCM NO. 43321	DWG. NO. FODST-COLOR	REV. B			
PROJECTION	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	<table border="1"> <tr> <td>SCALE: NONE</td> <td>CAD FILE: FODST-COLOR.SLDDRW</td> <td>SHEET 1 OF 2</td> </tr> </table>	SCALE: NONE	CAD FILE: FODST-COLOR.SLDDRW	SHEET 1 OF 2
SCALE: NONE	CAD FILE: FODST-COLOR.SLDDRW	SHEET 1 OF 2				

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC.. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

MODEL NO.	JACKET COLOR	LENGTH MTR [FT]
FODST-RD-01	RED	1 M [3.28 FT]
FODST-RD-02	RED	2 M [6.56 FT]
FODST-RD-03	RED	3 M [9.84 FT]
FODST-RD-04	RED	4 M [13.12 FT]
FODST-RD-05	RED	5 M [16.40 FT]
FODST-RD-10	RED	10 M [32.81 FT]
FODST-RD-15	RED	15 M [49.22 FT]
FODST-GR-01	GREEN	1 M [3.28 FT]
FODST-GR-02	GREEN	2 M [6.56 FT]
FODST-GR-03	GREEN	3 M [9.84 FT]
FODST-GR-04	GREEN	4 M [13.12 FT]
FODST-GR-05	GREEN	5 M [16.40 FT]
FODST-GR-10	GREEN	10 M [32.81 FT]
FODST-GR-15	GREEN	15 M [49.22 FT]
FODST-BL-01	BLUE	1 M [3.28 FT]
FODST-BL-02	BLUE	2 M [6.56 FT]
FODST-BL-03	BLUE	3 M [9.84 FT]
FODST-BL-04	BLUE	4 M [13.12 FT]
FODST-BL-05	BLUE	5 M [16.40 FT]
FODST-BL-10	BLUE	10 M [32.81 FT]
FODST-BL-15	BLUE	15 M [49.22 FT]
FODST-YL-01	YELLOW	1 M [3.28 FT]
FODST-YL-02	YELLOW	2 M [6.56 FT]
FODST-YL-03	YELLOW	3 M [9.84 FT]
FODST-YL-04	YELLOW	4 M [13.12 FT]
FODST-YL-05	YELLOW	5 M [16.40 FT]
FODST-YL-10	YELLOW	10 M [32.81 FT]
FODST-YL-15	YELLOW	15 M [49.22 FT]
FODST-OR-01	ORANGE	1 M [3.28 FT]
FODST-OR-02	ORANGE	2 M [6.56 FT]
FODST-OR-03	ORANGE	3 M [9.84 FT]
FODST-OR-04	ORANGE	4 M [13.12 FT]
FODST-OR-05	ORANGE	5 M [16.40 FT]
FODST-OR-10	ORANGE	10 M [32.81 FT]
FODST-OR-15	ORANGE	15 M [49.22 FT]

△ B

		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
CATEGORY <p style="text-align: center;">FIBER OPTICS</p>			
PRODUCT DESCRIPTION <p style="text-align: center;">SC-SC DPLX ASSEMBLY</p>			
SIZE A	FSCM NO. 43321	DWG. NO. FODST-COLOR	REV. B
SCALE: NONE		CAD FILE: FODST-COLOR.SLDDRW	
			SHEET 2 OF 2