


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	DRAWING REPLACES FODSTC50-01-OD1	6/24/14	D. DESJARDIN



PART NUMBER	LENGTH METERS [FEET]	PART NUMBER	LENGTH METERS [FEET]
FODSTC50-01	1.0 [3.3]	FODSTC50-30	30.0 [98.4]
FODSTC50-02	2.0 [6.6]	FODSTC50-35	35.0 [114.8]
FODSTC50-03	3.0 [9.8]	FODSTC50-40	40.0 [131.2]
FODSTC50-04	4.0 [13.1]	FODSTC50-45	45.0 [147.6]
FODSTC50-05	5.0 [16.4]	FODSTC50-50	50.0 [164.0]
FODSTC50-10	10.0 [32.8]	FODSTC50-75	75.0 [246.1]
FODSTC50-15	15.0 [49.2]	FODSTC50-100	100.0 [328.1]
FODSTC50-20	20.0 [65.6]	FODSTC50-125	125.0 [410.1]
FODSTC50-25	25.0 [82.0]	FODSTC50-150	150.0 [492.1]

NOTES:

- CONNECTOR ASSEMBLY POLISH TYPE: PC
- ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
- PACKAGING:
LESS THAN 50 METERS (164 FT): INDIVIDUALLY PACKAGE EACH ASSEMBLY IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.
50 METERS (164 FT) OR MORE: TO BE SPOOLED

REGULATORY COMPLIANCE:
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY RC	8/16/2000		
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [51] .XXX = ±.005 [1.27]	CHECKED BY ENG	8/16/2000	CATEGORY FIBER OPTICS	
	APPROVED BY AFC	8/16/2000	PRODUCT DESCRIPTION CA ST-ST 50/125 DUPLEX	
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321
			DWG. NO. FODSTC50	REV. A
	FODSTC50-01-OD1	SCALE: NONE	CAD FILE: FODSTC50.LDDRW	SHEET 1 OF 1