


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	3/12/12	D.GRIFFIN
B	ECN 6326: ADDED ROHS STAMP, ADDED 2X-SHRINK TUBE, REVISED LABEL INFO	8/7/12	D.FRISIELLO
C	ECN 6851: ADDED VENDOR P/N TO TABLE, UPDATED COMPLIANCE NOTE	5/22/13	D. DESJARDIN



L-COM P/N	METERS [FEET]	VENDOR P/N
FODULC-SNG-1M	1.0 [3.28]	ULC-SP2-001M
FODULC-SNG-2M	2.0 [6.56]	ULC-SP2-002M
FODULC-SNG-3M	3.0 [9.84]	ULC-SP2-003M
FODULC-SNG-4M	4.0 [13.12]	ULC-SP2-004M
FODULC-SNG-5M	5.0 [16.40]	ULC-SP2-005M
FODULC-SNG-6M	6.0 [19.69]	ULC-SP2-006M
FODULC-SNG-7M	7.0 [22.97]	ULC-SP2-007M

**NOTES:**

- CONNECTOR ASSEMBLY POLISH TYPE: PC
- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

**REGULATORY COMPLIANCE:**  
CE2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [51] .XXX = ±.005 [1.27]	APPROVALS D. DESJARDIN CHECKED BY D. GUITADAURO APPROVED BY D. GALLAGHER	DATE 3/12/12 3/12/12 3/12/12	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845		
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	CATEGORY <b>FIBER OPTICS</b>		PRODUCT DESCRIPTION <b>ULC-ULC 9/125 SNG OFNP</b>	
PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. <b>FODULC-SNG</b>	REV. <b>C</b>
		SCALE: NONE	CAD FILE: FODULC-SNG.SLDRW	SHEET 1 OF 1	