


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	12/18/02	MCCORMICK
B	ECN# 2641; REVISED FORMAT & TOLERANCE	12/04/06	MCCORMICK
B	ECN99999: ADDED END VIEW AND NOTE 3. UPDATED FORMAT	02/08/10	DFP



PART #	LENGTH FEET [METERS]
FODZMT-LC-01	3.28 [1.0]
FODZMT-LC-02	6.56 [2.0]
FODZMT-LC-03	9.84 [3.0]
FODZMT-LC-04	13.12 [4.0]
FODZMT-LC-05	16.40 [5.0]

- NOTES:
- CONNECTOR ASSEMBLY USES A PC POLISH.
 - ALL CONNECTORS ACCOMPANIED WITH A DUST CAP (NOT SHOWN).
 - CABLE ASSEMBLY SHALL BE PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 > 12 [305] ≤ 60 [1524] = +2 [51] / -0 > 60 [1524] ≤ 120 [3048] = +4 [102] / -0 > 120 [3048] ≤ 300 [7620] = +6 [152] / -0 > 300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 .XX = ± .02 .XXX = ± .005	APPROVALS DRAWN BY C.MCCORMICK CHECKED BY D.PARHAM APPROVED BY R.CARRICK	DATE 12/03/2002 12/03/2002 12/03/2002	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR	CATEGORY FIBER OPTIC PRODUCT DESCRIPTION 62.5/125 MTRJ LC LSZH CABLE ASSY		SCALE: NONE CAD FILE: FODZMT-LC.SLDDRW
PROJECTION 	SIZE A	FSCM NO. 43321	DWG. NO. FODZMT-LC	REV. B