



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	DRAWING REPLACES FOL-LC-OD1	10/2/14	D.FRISIELLO




CONNECTOR BRACKET



2X, LC CONNECTOR

62.5/125 MULTIMODE OM1 SIMPLEX FIBER
OFNR (RISER) RATED
JACKET: GRAY



NOTES:

1. CONNECTOR ASSEMBLY POLISH TYPE: PC
2. ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
3. CABLE O.D. RANGE: 1.6mm TO 3.0mm
4. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [51] .XXX = ±.005 [1.13]	APPROVALS DRAWN BY C.McCORMICK CHECKED BY DFP APPROVED BY R.CARRICK	DATE 01/11/01 01/19/01 01/19/01	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		CATEGORY FIBER OPTICS	
	COLOR VARIATIONS MAY OCCUR		PRODUCT DESCRIPTION LOOPBACK LC 62.5/125	
	PROJECTION 	SIZE A	FSCM NO. 43321	DWG. NO. FOL-LC

SCALE: NONE | CAD FILE: FOL-LC.SLDDRW | SHEET 1 OF 1