
8 7 6 5 4 3 2 1

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REV DESCRIPTION DATE APPROVED

A INITIAL RELEASE 07/09/2020 PHOSPODAR

PART NUMBER FIBER MODE		JACKET TYPE	CONNECTOR POLISH	METERS [FEET]	
FPT12-LCUSM-R-FO-3	9/125 SINGLE MODE OS2	OFNR (RISER) RATED	U (ULTRA)	3.0 [9.84]	



5

WIRING MAP				
FIBER #	SC COLOR			
1	BLUE			
2	ORANGE			
3	GREEN			
4	BROWN			
5	GRAY			
6	WHITE			
7	RED			
8	BLACK			
9	YELLOW			
10	PURPLE			
11	ROSE			
12	AQUA			

NOTES:

T-Rev.D

8

D

- 1. SEE CHARTS FOR PART NUMBERS, FIBER MODES, COLORS, AND LENGTHS.
- 2. LC CONNECTOR ASSEMBLY POLISH TYPE: SEE CHART
- 3. ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
- 4. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM PACKAGING SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]	APPROVALS	DATE		CO	m l	50 High Street, We North Andover, M		USA.
OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0	DRAWN BY DFRISIELLO	07/09/2020		an INFINITE		Phone: 1.800.341. 1.978.682.		
>12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0	CHECKED BY PHOSPODAR	07/09/2020	CATEGOR	RY				
>120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0	APPROVED BY PHOSPODAR	07/09/2020	FIBER OPTICS					
ALL OTHER DIMENSIONAL TOLERANCES:	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		12 Fiber Ribbon, 9µm SM LC/UPC Pigtail Fanout Kit					
THIRD-ANGLE PROJECTION	COLOR VARIATIONS MAY OCCUR		SIZE A	43321	ITEM NO.	2-LCUSM-R-F	0	A REV.
			SCALE:	NONE CAD F	ILE: FPT12-LCUSA	n-r-fo.slddrw	SHEET 1	OF 1
4	3			2		1		