

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

RoHS Compliant ✓

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	7/16/12	D.GRIFFIN




CHART A								
FPT9OM1-FC-12PK-1			FPT9OM1-FC-12PK-2			FPT9OM1-FC-12PK-3		
PART NUMBER	LENGTH M [FT]	COLOR	PART NUMBER	LENGTH M [FT]	COLOR	PART NUMBER	LENGTH M [FT]	COLOR
FPT9OM1-FC-BLK-1	1.0 [3.28]	BLACK	FPT9OM1-FC-BLK-2	2.0 [6.56]	BLACK	FPT9OM1-FC-BLK-3	3.0 [9.84]	BLACK
FPT9OM1-FC-ORG-1	1.0 [3.28]	ORANGE	FPT9OM1-FC-ORG-2	2.0 [6.56]	ORANGE	FPT9OM1-FC-ORG-3	3.0 [9.84]	ORANGE
FPT9OM1-FC-YLW-1	1.0 [3.28]	YELLOW	FPT9OM1-FC-YLW-2	2.0 [6.56]	YELLOW	FPT9OM1-FC-YLW-3	3.0 [9.84]	YELLOW
FPT9OM1-FC-GRY-1	1.0 [3.28]	GRAY	FPT9OM1-FC-GRY-2	2.0 [6.56]	GRAY	FPT9OM1-FC-GRY-3	3.0 [9.84]	GRAY
FPT9OM1-FC-BLU-1	1.0 [3.28]	BLUE	FPT9OM1-FC-BLU-2	2.0 [6.56]	BLUE	FPT9OM1-FC-BLU-3	3.0 [9.84]	BLUE
FPT9OM1-FC-GRN-1	1.0 [3.28]	GREEN	FPT9OM1-FC-GRN-2	2.0 [6.56]	GREEN	FPT9OM1-FC-GRN-3	3.0 [9.84]	GREEN
FPT9OM1-FC-AQU-1	1.0 [3.28]	AQUA	FPT9OM1-FC-AQU-2	2.0 [6.56]	AQUA	FPT9OM1-FC-AQU-3	3.0 [9.84]	AQUA
FPT9OM1-FC-BRN-1	1.0 [3.28]	BROWN	FPT9OM1-FC-BRN-2	2.0 [6.56]	BROWN	FPT9OM1-FC-BRN-3	3.0 [9.84]	BROWN
FPT9OM1-FC-RED-1	1.0 [3.28]	RED	FPT9OM1-FC-RED-2	2.0 [6.56]	RED	FPT9OM1-FC-RED-3	3.0 [9.84]	RED
FPT9OM1-FC-WHT-1	1.0 [3.28]	WHITE	FPT9OM1-FC-WHT-2	2.0 [6.56]	WHITE	FPT9OM1-FC-WHT-3	3.0 [9.84]	WHITE
FPT9OM1-FC-VIO-1	1.0 [3.28]	VIOLET	FPT9OM1-FC-VIO-2	2.0 [6.56]	VIOLET	FPT9OM1-FC-VIO-3	3.0 [9.84]	VIOLET
FPT9OM1-FC-ROS-1	1.0 [3.28]	ROSE	FPT9OM1-FC-ROS-2	2.0 [6.56]	ROSE	FPT9OM1-FC-ROS-3	3.0 [9.84]	ROSE

NOTES:

1. FC CONNECTOR ASSEMBLY POLISH TYPE: PC.
2. ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
3. CABLE ASSEMBLY SHALL BE PACKAGED 12 PIECES PER BAG IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 >12 [305] ≤ 60 [1524] = +2 [51] / -0 >60 [1524] ≤ 120 [3048] = +4 [102] / -0 >120 [3048] ≤ 300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 .XX = ± .02 .XXX = ± .005	APPROVALS DRAWN BY D.PARHAM CHECKED BY D.GUITADAURO APPROVED BY D.GALLAGHER	DATE 05/11/2012 05/15/2012 07/13/2012	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	CATEGORY FIBER OPTIC	
PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321
		DWG. NO. FPT9OM1-FC-12PK	REV. A
		SCALE: NONE	CAD FILE: FPT9OM1-FC-12PK.SLDDRW
		SHEET 1 OF 1	